



FITA GUIA



PTFE BRONZE
PTFE GRAFITADO

Velocidade até 15 Metros Segundo
Temperatura -100 até +120



ORKOT
Poliéster Sintético + Resina

Velocidade até 25 Metros Segundo
Temperatura até +140

ANEIS GUIA



AGI / AGE
POM + VIDRO

Pressão ilimitada
Temperatura -40 até +110



IBR / EBR
POM

Velocidade 1 Metros Segundo
Temperatura -40 até +110



ANEL GUIA " T "
POM

Velocidade 1 Metros Segundo
Temperatura -40 até +110

| POS. | DESIGNAÇÃO | MEDIDA | MATERIAL |
|------|------------------|-------------------|--------------|
| 1 | FITA GUIA | 3,00X1,50 | PTFE BRONZE |
| 2 | FITA GUIA | 3,20X1,50 | PTFE BRONZE |
| 3 | FITA GUIA | 3,50X1,80 | PTFE BRONZE |
| 4 | FITA GUIA | 3,60X1,55 | PTFE BRONZE |
| 5 | FITA GUIA | 4,20X1,50 | PTFE BRONZE |
| 6 | FITA GUIA | 4,20X2,00 | PTFE BRONZE |
| 7 | FITA GUIA | 4,20X2,50 | PTFE BRONZE |
| 8 | FITA GUIA | 4,40X1,50 | PTFE BRONZE |
| 9 | FITA GUIA | 5,00X2,00 | PTFE BRONZE |
| 10 | FITA GUIA | 5,60X1,50 | PTFE BRONZE |
| 11 | FITA GUIA | 5,60X2,00 | PTFE BRONZE |
| 12 | FITA GUIA | 5,60X2,50 | PTFE BRONZE |
| 13 | FITA GUIA | 6,00X2,00 | PTFE BRONZE |
| 14 | FITA GUIA | 6,00X2,50 | PTFE BRONZE |
| 15 | FITA GUIA | 6,30X1,50 | PTFE BRONZE |
| 16 | FITA GUIA | 6,30X2,00 | PTFE BRONZE |
| 17 | FITA GUIA | 6,30X2,50 | PTFE BRONZE |
| 18 | FITA GUIA | 7,00X1,00 | PTFE BRONZE |
| 19 | FITA GUIA | 7,20X1,00 | PTFE BRONZE |
| 20 | FITA GUIA | 8,00X1,00 | PTFE BRONZE |
| 21 | FITA GUIA | 8,00X1,50 | PTFE BRONZE |
| 22 | FITA GUIA | 8,00X2,00 | PTFE BRONZE |
| 23 | FITA GUIA | 8,00X3,00 | PTFE BRONZE |
| 24 | FITA GUIA | 8,00X4,00 | PTFE BRONZE |
| 25 | FITA GUIA | 8,00X5,00 | PTFE BRONZE |
| 26 | FITA GUIA | 8,10X1,50 | PTFE BRONZE |
| 27 | FITA GUIA | 8,10X2,00 | PTFE BRONZE |
| 28 | FITA GUIA | 8,10X2,50 | PTFE BRONZE |
| 29 | FITA GUIA | 9,50X2,50 | PTFE BRONZE |
| 30 | FITA GUIA | 9,70X2,00 | PTFE BRONZE |
| 31 | FITA GUIA | 9,70X2,50 | ORKOT |
| 32 | FITA GUIA | 9,70X2,50 | PTFE BRONZE |
| 33 | FITA GUIA | 9,70X3,00 | PTFE BRONZE |
| 34 | FITA GUIA | 9,70X4,00 | PTFE BRONZE |
| 35 | FITA GUIA | 10,00X1,00 | PTFE BRONZE |
| 36 | FITA GUIA | 10,00X1,20 | PTFE BRONZE |
| 37 | FITA GUIA | 10,00X1,50 | PTFE BRONZE |
| 38 | FITA GUIA | 10,00X2,00 | PTFE BRONZE |
| 39 | FITA GUIA | 10,00X2,50 | PTFE BRONZE |
| 40 | FITA GUIA | 10,00X3,00 | ORKOT |
| 41 | FITA GUIA | 10,00X3,00 | PTFE BRONZE |
| 42 | FITA GUIA | 10,00X4,50 | PTFE BRONZE |
| 43 | FITA GUIA | 12,00X2,00 | PTFE BRONZE |
| 44 | FITA GUIA | 12,00X2,50 | ORKOT |
| 45 | FITA GUIA | 12,00X2,50 | PTFE BRONZE |
| 46 | FITA GUIA | 12,00X3,00 | PTFE BRONZE |
| 47 | FITA GUIA | 12,70X1,50 | PTFE BRONZE |
| 48 | FITA GUIA | 13,00X2,50 | PTFE BRONZE |
| 49 | FITA GUIA | 13,00X3,00 | PTFE BRONZE |
| 50 | FITA GUIA | 14,00X2,00 | PTFE BRONZE |
| 51 | FITA GUIA | 14,80X2,40 | PTFE BRONZE |
| 52 | FITA GUIA | 15,00X1,50 | PTFE BRONZE |
| 53 | FITA GUIA | 15,00X2,00 | PTFE BRONZE |
| 54 | FITA GUIA | 15,00X2,50 | ORKOT |
| 55 | FITA GUIA | 15,00X2,50 | PTFE BRONZE |
| 56 | FITA GUIA | 15,00X3,00 | PTFE BRONZE |
| 57 | FITA GUIA | 18,00X2,00 | PTFE BRONZE |



| POS. | DESIGNAÇÃO | MEDIDA | MATERIAL |
|------|------------------|--------------------|--------------|
| 58 | FITA GUIA | 19,00X2,40 | PTFE BRONZE |
| 59 | FITA GUIA | 19,00X3,00 | PTFE BRONZE |
| 60 | FITA GUIA | 20,00X1,50 | PTFE BRONZE |
| 61 | FITA GUIA | 20,00X2,00 | PTFE BRONZE |
| 62 | FITA GUIA | 20,00X2,50 | ORKOT |
| 63 | FITA GUIA | 20,00X2,50 | PTFE BRONZE |
| 64 | FITA GUIA | 20,00X3,000 | ORKOT |
| 65 | FITA GUIA | 20,00X3,00 | PTFE BRONZE |
| 66 | FITA GUIA | 20,00X4,00 | PTFE BRONZE |
| 67 | FITA GUIA | 24,50X4,00 | PTFE BRONZE |
| 68 | FITA GUIA | 25,00X2,00 | PTFE BRONZE |
| 69 | FITA GUIA | 25,00X2,50 | ORKOT |
| 70 | FITA GUIA | 25,00X2,50 | PTFE BRONZE |
| 71 | FITA GUIA | 25,00X3,000 | ORKOT |
| 72 | FITA GUIA | 25,00X3,00 | PTFE BRONZE |
| 73 | FITA GUIA | 25,00X4,00 | PTFE BRONZE |
| 74 | FITA GUIA | 30,00X1,50 | PTFE BRONZE |
| 75 | FITA GUIA | 30,00X2,00 | PTFE BRONZE |
| 76 | FITA GUIA | 30,00X2,50 | ORKOT |
| 77 | FITA GUIA | 30,00X2,50 | PTFE BRONZE |
| 78 | FITA GUIA | 30,00X3,00 | PTFE BRONZE |
| 79 | FITA GUIA | 35,00X1,50 | PTFE BRONZE |
| 80 | FITA GUIA | 35,00X2,00 | PTFE BRONZE |
| 81 | FITA GUIA | 35,00X2,50 | ORKOT |
| 82 | FITA GUIA | 35,00X2,50 | PTFE BRONZE |
| 83 | FITA GUIA | 35,00X3,00 | PTFE BRONZE |
| 84 | FITA GUIA | 35,00X5,00 | PTFE BRONZE |
| 85 | FITA GUIA | 39,00X1,50 | PTFE BRONZE |
| 86 | FITA GUIA | 39,70X2,40 | PTFE BRONZE |
| 87 | FITA GUIA | 40,00X1,50 | PTFE BRONZE |
| 88 | FITA GUIA | 40,00X2,00 | PTFE BRONZE |
| 89 | FITA GUIA | 40,00X2,50 | ORKOT |
| 90 | FITA GUIA | 40,00X2,50 | PTFE BRONZE |
| 91 | FITA GUIA | 40,00X3,00 | PTFE BRONZE |
| 92 | FITA GUIA | 40,00X4,00 | PTFE BRONZE |
| 93 | FITA GUIA | 45,00X1,50 | PTFE BRONZE |
| 94 | FITA GUIA | 45,00X2,50 | PTFE BRONZE |
| 95 | FITA GUIA | 50,00X1,50 | PTFE BRONZE |
| 96 | FITA GUIA | 50,00X2,00 | PTFE BRONZE |
| 97 | FITA GUIA | 50,00X2,50 | PTFE BRONZE |
| 98 | FITA GUIA | 50,00X3,00 | PTFE BRONZE |
| 99 | FITA GUIA | 50,00X4,00 | PTFE BRONZE |
| 100 | FITA GUIA | 60,00X1,50 | PTFE BRONZE |
| 101 | FITA GUIA | 60,00X2,50 | PTFE BRONZE |
| 102 | FITA GUIA | 65,00X1,50 | PTFE BRONZE |
| 103 | FITA GUIA | 65,00X3,00 | PTFE BRONZE |
| 104 | FITA GUIA | 70,00X1,50 | PTFE BRONZE |
| 105 | FITA GUIA | 75,00X1,50 | PTFE BRONZE |
| 106 | FITA GUIA | 80,00X1,50 | PTFE BRONZE |
| 107 | FITA GUIA | 80,00X3,00 | PTFE BRONZE |
| 108 | FITA GUIA | 100,00X1,50 | PTFE BRONZE |
| 109 | FITA GUIA | 110,00X2,50 | PTFE BRONZE |
| 110 | FITA GUIA | 125,00X1,50 | PTFE BRONZE |
| 111 | FITA GUIA | 130,00X1,50 | PTFE BRONZE |
| 112 | FITA GUIA | 230,00X1,50 | PTFE BRONZE |
| 113 | FITA GUIA | 230,00X2,50 | PTFE BRONZE |



| POS. | DESIGNAÇÃO | REFERÊNCIA | MEDIDA |
|------|------------|-----------------|-------------------------|
| 1 | ANEL GUIA | AG0050/3I | 5X8X4 |
| 2 | ANEL GUIA | AG0070/3I | 7X10X4 |
| 3 | ANEL GUIA | AG0090/3I | 9X12X4 |
| 4 | ANEL GUIA | AGE016 | 12X16X9,60 |
| 5 | ANEL GUIA | AGI012 | 12X16X9,60 |
| 6 | ANEL GUIA | AGI014 | 14X18X9,60 |
| 7 | ANEL GUIA | AGE020 | 16X20X9,60 |
| 8 | ANEL GUIA | AGI016 | 16X20X9,60 |
| 9 | ANEL GUIA | AGI018 | 18X22X9,60 |
| 10 | ANEL GUIA | EBR025 | 19X25X10 |
| 11 | ANEL GUIA | EBR1000 | 19,41X25,4X9,98 |
| 12 | ANEL GUIA | AGI020 | 20X24X9,60 |
| 13 | ANEL GUIA | IBR020 | 20X26X10 |
| 14 | ANEL GUIA | AGE025 | 21X25X9,6 |
| 15 | ANEL GUIA | AGE035 | 21X35X9,6 |
| 16 | ANEL GUIA | AGI022 | 22X26X9,60 |
| 17 | ANEL GUIA | KT200/22 | 22X27X5,60 |
| 18 | ANEL GUIA | IBR022 | 22X28X10 |
| 19 | ANEL GUIA | AG0250/3I | 25X28X4 |
| 20 | ANEL GUIA | AGI025 | 25X29X9,60 |
| 21 | ANEL GUIA | IBR025 | 25X31X10 |
| 22 | ANEL GUIA | IBR1000 | 25,40X31,39X9,98 |
| 23 | ANEL GUIA | EBR1250 | 25,76X31,75X9,98 |
| 24 | ANEL GUIA | AGE030 | 26X30X9,6 |
| 25 | ANEL GUIA | AGI026 | 26X30X9,6 |
| 26 | ANEL GUIA | EBR032 | 26X32X10 |
| 27 | ANEL GUIA | IBR026 | 26X32X10 |
| 28 | ANEL GUIA | AG0270/3I | 27X30X4 |
| 29 | ANEL GUIA | AGE032 | 28X32X10 |
| 30 | ANEL GUIA | AGI028 | 28X32X9,60 |
| 31 | ANEL GUIA | IBR028 | 28X34X10 |
| 32 | ANEL GUIA | IBR1125 | 28,57X34,57X9,98 |
| 33 | ANEL GUIA | EBR1375 | 28,93X34,92X9,98 |
| 34 | ANEL GUIA | GF2/3330 | 30X33X3 |
| 35 | ANEL GUIA | AG0300/3I | 30X33X4 |
| 36 | ANEL GUIA | AGI030 | 30X34X9,60 |
| 37 | ANEL GUIA | AGI030/1 | 30X35X9,6 |
| 38 | ANEL GUIA | EBR036 | 30X36X10 |
| 39 | ANEL GUIA | IBR030 | 30X36X10 |
| 40 | ANEL GUIA | IBR031 | 31X37X10 |
| 41 | ANEL GUIA | IBR1250 | 31,75X37,74X9,98 |
| 42 | ANEL GUIA | AGI032 | 32X36X9,60 |
| 43 | ANEL GUIA | PBR032037097 | 32X37X9,70 |
| 44 | ANEL GUIA | AGI032/1 | 32X38X9,80 |
| 45 | ANEL GUIA | IBR032 | 32X38X10 |
| 46 | ANEL GUIA | EBR1500 | 32,11X38,10X9,98 |
| 47 | ANEL GUIA | AG0330/3I | 33X36X4 |
| 48 | ANEL GUIA | EBR040 | 34X40X10 |
| 49 | ANEL GUIA | IBR034 | 34X40X10 |
| 50 | ANEL GUIA | IBR1375 | 34,92X40,92X9,98 |
| 51 | ANEL GUIA | AGI035 | 35X39X9,98 |
| 52 | ANEL GUIA | I/DW35/2 | 35X39X9,60 |
| 53 | ANEL GUIA | AGE040/1 | 35X40X6,1 |
| 54 | ANEL GUIA | AGI035/1 | 35X41X9,60 |



| POS. | DESIGNAÇÃO | REFERÊNCIA | MEDIDA |
|-----------|------------------------|------------------|-------------------------|
| 55 | ANEL GUIA | IBR035 | 35X41X10 |
| 56 | ANEL GUIA | EBR1625 | 35,28X41,28X9,98 |
| 57 | ANEL GUIA | AG0360/3I | 36X40X8 |
| 58 | ANEL GUIA | AGE040 | 36X40X9,60 |
| 59 | ANEL GUIA | AGE40 | 36X40X9,6 |
| 60 | ANEL GUIA | IBR036 | 36X42X10 |
| 61 | ANEL GUIA | AG0370/3I | 37X40X4 |
| 62 | ANEL GUIA | AGI038 | 38X42X9,60 |
| 63 | ANEL GUIA | IBR1500 | 38,10X44,09X9,98 |
| 64 | ANEL GUIA | EBR1750 | 38,45X44,45X9,98 |
| 65 | ANEL GUIA | EBR1750/1 | 38,45X44,45X13 |
| 66 | ANEL GUIA | AG0390/3I | 39X42X4 |
| 67 | ANEL GUIA | EBR045 | 39X45X10 |
| 68 | ANEL GUIA | AGI036 | 40X36X9,6 |
| 69 | ANEL GUIA | AGI040 | 40X44X9,60 |
| 70 | ANEL GUIA | AGI040/2 | 40X45X9,5 |
| 71 | ANEL GUIA | KT200/40 | 40X45X9,7 |
| 72 | ANEL GUIA | AGI040/1 | 40X46X9,60 |
| 73 | ANEL GUIA | EBR046 | 40X46X10 |
| 74 | ANEL GUIA | IBR040 | 40X46X10 |
| 75 | ANEL GUIA | PORT4046127 | 40X46X12,70 |
| 76 | ANEL GUIA | AG0400/3I | 40X47X9,70 |
| 77 | ANEL GUIA | AGE045 | 45X41X9,60 |
| 78 | ANEL GUIA | AGE45 | 41X45X9,6 |
| 79 | ANEL GUIA | IBR042 | 42X48X13 |
| 80 | ANEL GUIA | AGE050 | 44X50X9,60 |
| 81 | ANEL GUIA | EBR050/1 | 44X50X13 |
| 82 | ANEL GUIA | IBR1750 | 44,45X50,44X9,98 |
| 83 | ANEL GUIA | IBR1750/1 | 44,45X50,44X13,00 |
| 84 | ANEL GUIA | EBR2000 | 44,81X50,80X9,98 |
| 85 | ANEL GUIA | EBR2000/1 | 44,81X50,80X13 |
| 86 | ANEL GUIA | AGI045/3 | 45X50X5,6 |
| 87 | ANEL GUIA | AGI045/2 | 45X50X9,70 |
| 88 | ANEL GUIA | KT200/45 | 45X50X9,7 |
| 89 | ANEL GUIA | IDWR45/3 | 45X50X12,50 |
| 90 | ANEL GUIA | PBR045050150 | 45X50X15 |
| 91 | ANEL GUIA | AGI045 | 45X51X9,60 |
| 92 | ANEL GUIA | AGI045/1 | 45X51X12,50 |
| 93 | ANEL GUIA " T " | T7750 | 46X51,50X27 |
| 94 | ANEL GUIA | AGI046 | 46X52X9,60 |
| 95 | ANEL GUIA | EBR2125 | 47,98X53,97X13 |
| 96 | ANEL GUIA | PBR048053150 | 48X53X15 |
| 97 | ANEL GUIA | AGI048 | 48X54X9,60 |
| 98 | ANEL GUIA | AGI048/1 | 48X54X12,8 |
| 99 | ANEL GUIA | AGE055 | 49X55X12,80 |
| 100 | ANEL GUIA | E/DWR-50 | 50X44X9,60 |
| 101 | ANEL GUIA | WR050/1 | 50X55X5,6 |
| 102 | ANEL GUIA | AGI050/1 | 50X55X9,7 |
| 103 | ANEL GUIA | KT200/50 | 50X55X9,7 |
| 104 | ANEL GUIA | AGI050 | 50X56X9,60 |
| 105 | ANEL GUIA | IDWR50/3 | 50X56X12,80 |
| 106 | ANEL GUIA | EBR056 | 50X56X13 |
| 107 | ANEL GUIA | IBR050 | 50X56X13 |
| 108 | ANEL GUIA | AG0502E-22 | 50,20X55,20X9,70 |



| POS. | DESIGNAÇÃO | REFERÊNCIA | MEDIDA |
|------------|------------------------|----------------|-----------------------|
| 109 | ANEL GUIA | IBR2000 | 50,80X56,79X13,00 |
| 110 | ANEL GUIA | EBR2250 | 51,15X57,15X13 |
| 111 | ANEL GUIA | AGI053 | 53X59X9,60 |
| 112 | ANEL GUIA | IBR2125/1 | 53,97X59,97X13,00 |
| 113 | ANEL GUIA | AGE060 | 54X60X12,80 |
| 114 | ANEL GUIA | E/DWR-60 | 54X60X12,8 |
| 115 | ANEL GUIA | EBR2375 | 54,33X60,32X13 |
| 116 | ANEL GUIA | E/DWR-55 | 55X49X12,80 |
| 117 | ANEL GUIA | AGE60/1 | 55X60X9,70 |
| 118 | ANEL GUIA | PBR055060150 | 55X60X15 |
| 119 | ANEL GUIA | AGI055 | 55X61X9,60 |
| 120 | ANEL GUIA | I/DWR55 | 55X61X9,70 |
| 121 | ANEL GUIA | AGI55/1 | 55X61X12,70 |
| 122 | ANEL GUIA | IBR055 | 55X61X13 |
| 123 | ANEL GUIA " T " | T7756 | 55X61X27 |
| 124 | ANEL GUIA | IBR056 | 56X62X13 |
| 125 | ANEL GUIA | EBR063 | 57X63X13 |
| 126 | ANEL GUIA | IBR2250 | 57,15X63,14X13,00 |
| 127 | ANEL GUIA | W250037 | 57,15X63,50X9,52 |
| 128 | ANEL GUIA | EBR2500 | 57,51X63,50X13 |
| 129 | ANEL GUIA | AG0580/11 | 58,00X63,00X9,70 |
| 130 | ANEL GUIA | KT200/58 | 58X63X9,7 |
| 131 | ANEL GUIA | KT200/59 | 59X63X9,7 |
| 132 | ANEL GUIA | PORT596310 | 59X63X10 |
| 133 | ANEL GUIA | AGE065 | 59X65X12,80 |
| 134 | ANEL GUIA | ESRF060X5.5 | 60X65X5.5 |
| 135 | ANEL GUIA | SB60 | 60X65X9,60 |
| 136 | ANEL GUIA | AGI060/1 | 60X65X9.70 |
| 137 | ANEL GUIA | KT200/6/1 | 60X65X9,7 |
| 138 | ANEL GUIA | PORT606597 | 60X65X9,70 |
| 139 | ANEL GUIA | KT200/60 | 60X65X15 |
| 140 | ANEL GUIA | PBR060065160 | 60X65X16 |
| 141 | ANEL GUIA | AGI060 | 60X66X12,80 |
| 142 | ANEL GUIA | IBR2375 | 60,33X66,32X13,00 |
| 143 | ANEL GUIA " T " | T7751 | 61X66,50X27 |
| 144 | ANEL GUIA | AGI063 | 63X69X12,80 |
| 145 | ANEL GUIA | IBR2500 | 63,50X69,49X13,00 |
| 146 | ANEL GUIA | AGE070 | 64X70X12,80 |
| 147 | ANEL GUIA | PBR065070097 | 65X70X9,70 |
| 148 | ANEL GUIA | AGI065 | 65X71X12,80 |
| 149 | ANEL GUIA " T " | T7757 | 65X71X27 |
| 150 | ANEL GUIA | IBR2625 | 66,67X72,67X13,00 |
| 151 | ANEL GUIA | EBR074 | 68X74X13 |
| 152 | ANEL GUIA | AGE075 | 69X75X12,80 |
| 153 | ANEL GUIA | IBR2750 | 69,85X75,84X13,00 |
| 154 | ANEL GUIA | KT200/70 | 70X75X9,70 |
| 155 | ANEL GUIA | PBR070075150 | 70X75X15 |
| 156 | ANEL GUIA | PORT707515 | 70X75X15 |
| 157 | ANEL GUIA | AGI070 | 70X76X12,80 |
| 158 | ANEL GUIA " T " | T7891 | 70X78X20 |
| 159 | ANEL GUIA | IBR2875 | 73,02X79,02X13,00 |
| 160 | ANEL GUIA | EBR3125 | 73,38X79,37X13 |
| 161 | ANEL GUIA | AGE080 | 74X80X12,80 |
| 162 | ANEL GUIA | AGI075/1 | 75X80X9,7 |



| POS. | DESIGNAÇÃO | REFERÊNCIA | MEDIDA |
|------------|------------------------|----------------|-----------------------|
| 163 | ANEL GUIA | AGI75/1 | 75X80X9,70 |
| 164 | ANEL GUIA | PORT758097 | 75X80X9,70 |
| 165 | ANEL GUIA | KT200/75 | 75X80X15 |
| 166 | ANEL GUIA | AGI075 | 75X81X12,80 |
| 167 | ANEL GUIA " T " | T7758 | 75X81X27 |
| 168 | ANEL GUIA " T " | T7752 | 76X81,50X27 |
| 169 | ANEL GUIA | EBR082 | 76X82X13 |
| 170 | ANEL GUIA | IBR3000 | 76,20X82,19X13,00 |
| 171 | ANEL GUIA | EBR3250 | 76,55X82,55X13 |
| 172 | ANEL GUIA | AGE085 | 79X85X12,80 |
| 173 | ANEL GUIA | AGI80/1 | 80X85X9,70 |
| 174 | ANEL GUIA | PORT808597 | 80X85X9,70 |
| 175 | ANEL GUIA | AGI080 | 80X86X12,80 |
| 176 | ANEL GUIA | IBR3250 | 82,55X88,54X13,00 |
| 177 | ANEL GUIA | EBR3500 | 82,91X88,90X13 |
| 178 | ANEL GUIA | AGE090 | 84X90X12,80 |
| 179 | ANEL GUIA | KT200/85 | 85X90X15 |
| 180 | ANEL GUIA | PBR085090150 | 85X90X15 |
| 181 | ANEL GUIA | AGI085 | 85X91X12,80 |
| 182 | ANEL GUIA " T " | T7759 | 85X91X27 |
| 183 | ANEL GUIA | IBR3375 | 85,72X91,72X13,00 |
| 184 | ANEL GUIA | AG0889E-22 | 88,90X93,90X9,70 |
| 185 | ANEL GUIA | IBR3500 | 88,90X94,89X13,00 |
| 186 | ANEL GUIA | AGE095 | 89X95X12,80 |
| 187 | ANEL GUIA | KT200/90 | 90X84X14,70 |
| 188 | ANEL GUIA | AGI095/1 | 90X95X9,7 |
| 189 | ANEL GUIA | AGI090 | 90X96X12,80 |
| 190 | ANEL GUIA " T " | T7753 | 91X96,50X27 |
| 191 | ANEL GUIA | IBR3625 | 92,07X98,07X13,00 |
| 192 | ANEL GUIA | AGE100 | 94X100X12,80 |
| 193 | ANEL GUIA | KT200/95 | 95X89X24,40 |
| 194 | ANEL GUIA | DFA95100 | 95X100X9,5 |
| 195 | ANEL GUIA | PORT9510097 | 95X100X9,70 |
| 196 | ANEL GUIA | KT200/95/1 | 95X100X15 |
| 197 | ANEL GUIA | PBR095100150 | 95X100X15 |
| 198 | ANEL GUIA | PORT9510015 | 95X100X15 |
| 199 | ANEL GUIA | AGI095 | 95X101X12,80 |
| 200 | ANEL GUIA " T " | T7760 | 95X101X31 |
| 201 | ANEL GUIA " T " | T8172 | 95X102X31 |
| 202 | ANEL GUIA | IBR3750 | 95,25X101,24X13,00 |
| 203 | ANEL GUIA | AGE105 | 99X105X12,80 |
| 204 | ANEL GUIA | KT200/100 | 100X94X14,87 |
| 205 | ANEL GUIA | AGI100 | 100X106X12,80 |
| 206 | ANEL GUIA | PBR100106150 | 100X106X15 |
| 207 | ANEL GUIA | IBR100/2 | 100X106X19,60 |
| 208 | ANEL GUIA | IBR100/1 | 100X106X20,50 |
| 209 | ANEL GUIA | IBR4000 | 101,60X107,59X13,00 |
| 210 | ANEL GUIA | AGE110 | 104X110X12,80 |
| 211 | ANEL GUIA | FPO110 | 105X110X9,70 |
| 212 | ANEL GUIA | PBR105110150 | 105X110X15 |
| 213 | ANEL GUIA | AGI105 | 105X111X12,80 |
| 214 | ANEL GUIA " T " | T7761 | 105X111X31 |
| 215 | ANEL GUIA " T " | T7754 | 107X112,50X27 |
| 216 | ANEL GUIA | IBR4250 | 107,95X113,94X13,00 |



| POS. | DESIGNAÇÃO | REFERÊNCIA | MEDIDA |
|------------|------------------------|------------------|----------------------------|
| 217 | ANEL GUIA | AGE115 | 109X115X12,80 |
| 218 | ANEL GUIA | EBR115/1 | 109X115X19,50 |
| 219 | ANEL GUIA | AGI110 | 110X116X12,80 |
| 220 | ANEL GUIA | IBR4375 | 111,12X117,12X13,00 |
| 221 | ANEL GUIA | GF1/120112 | 112X120X9,7 |
| 222 | ANEL GUIA | AGE120 | 114X120X12,80 |
| 223 | ANEL GUIA | EBR120/1 | 114X120X19,50 |
| 224 | ANEL GUIA | IBR4500 | 114,30X120,29X13,00 |
| 225 | ANEL GUIA | KT200/115 | 115X109X14,70 |
| 226 | ANEL GUIA | AGI115 | 115X121X12,80 |
| 227 | ANEL GUIA " T " | T7762 | 115X121X31 |
| 228 | ANEL GUIA | IBR116 | 116X122X13 |
| 229 | ANEL GUIA | AGE125 | 119X125X12,80 |
| 230 | ANEL GUIA | DFA120125 | 120X125X14,5 |
| 231 | ANEL GUIA | AGI120 | 120X126X12,80 |
| 232 | ANEL GUIA " T " | T8173 | 120X127X31 |
| 233 | ANEL GUIA | IBR4750 | 120,65X126,64X13,00 |
| 234 | ANEL GUIA | EKF125121 | 121X125X20 |
| 235 | ANEL GUIA | EBR127 | 121X127X13 |
| 236 | ANEL GUIA | EBR5000 | 121X127,00X13 |
| 237 | ANEL GUIA | AGE130 | 124X130X12,80 |
| 238 | ANEL GUIA | PBR125130097 | 125X130X9,70 |
| 239 | ANEL GUIA | AGI125 | 125X131X12,80 |
| 240 | ANEL GUIA | IBR125/1 | 125X131X25,50 |
| 241 | ANEL GUIA " T " | T7763 | 125X131X31 |
| 242 | ANEL GUIA " T " | T7755 | 126X131,50X27 |
| 243 | ANEL GUIA | IBR5000 | 127,00X132,99X13,00 |
| 244 | ANEL GUIA | EBR5250 | 127,36X133,35X13 |
| 245 | ANEL GUIA | AGE135 | 129X135X12,80 |
| 246 | ANEL GUIA | AGI130 | 130X136X12,80 |
| 247 | ANEL GUIA | EBR5375 | 130,53X136,52X13 |
| 248 | ANEL GUIA | EBR5500 | 133,71X139,70X13 |
| 249 | ANEL GUIA | AGE140 | 134X140X12,80 |
| 250 | ANEL GUIA | AGI135 | 135X141X12,80 |
| 251 | ANEL GUIA " T " | T7764 | 135X141X31 |
| 252 | ANEL GUIA | IBR137 | 137X143X13 |
| 253 | ANEL GUIA | AGE145 | 139X145X12,80 |
| 254 | ANEL GUIA | IBR5500 | 139,70X145,69X13,00 |
| 255 | ANEL GUIA | PBR140145150 | 140X145X15 |
| 256 | ANEL GUIA | AGI140 | 140X146X12,80 |
| 257 | ANEL GUIA | EBR5750 | 140,04X146,05X13 |
| 258 | ANEL GUIA | AGE150 | 144X150X12,80 |
| 259 | ANEL GUIA | EBR150/1 | 144X150X19,50 |
| 260 | ANEL GUIA | AGI145 | 145X151X12,80 |
| 261 | ANEL GUIA " T " | T8174 | 145X152X31 |
| 262 | ANEL GUIA | IBR5750 | 146,05X152,04X13,00 |
| 263 | ANEL GUIA | IBR5750/1 | 146,05X152,04X19,48 |
| 264 | ANEL GUIA | EBR6000 | 146,41X152,40X13 |
| 265 | ANEL GUIA | AGE155 | 149X155X19,20 |
| 266 | ANEL GUIA | PBR150155150 | 150X155X15 |
| 267 | ANEL GUIA | AGI150 | 150X156X12,80 |
| 268 | ANEL GUIA | IBR150 | 150X156X19,50 |
| 269 | ANEL GUIA | AGE160 | 154X160X19,20 |
| 270 | ANEL GUIA | DFA155160 | 155X160X14,6 |



| POS. | DESIGNAÇÃO | REFERÊNCIA | MEDIDA |
|------|------------|-----------------|----------------------------|
| 271 | ANEL GUIA | AGI155 | 155X161X19,20 |
| 272 | ANEL GUIA | AGE165 | 159X165X19,20 |
| 273 | ANEL GUIA | AG1600/2E | 160,00X155,00X8,10 |
| 274 | ANEL GUIA | AGI160 | 160X166X19,20 |
| 275 | ANEL GUIA | AGE170 | 164X170X19,20 |
| 276 | ANEL GUIA | AGI165 | 165X171X19,20 |
| 277 | ANEL GUIA | AGE175 | 169X175X19,20 |
| 278 | ANEL GUIA | AGI170 | 170X176X19,20 |
| 279 | ANEL GUIA | EBR7000 | 171,81X177,80X19,51 |
| 280 | ANEL GUIA | GF1/180172 | 172X180X9,7 |
| 281 | ANEL GUIA | AGE180 | 174X180X19,20 |
| 282 | ANEL GUIA | AGE180/1 | 175X180X14,60 |
| 283 | ANEL GUIA | AGI175 | 175X181X19,20 |
| 284 | ANEL GUIA | AGE185 | 179X185X19,20 |
| 285 | ANEL GUIA | AGI180 | 180X186X19,20 |
| 286 | ANEL GUIA | AGE190 | 184X190X19,20 |
| 287 | ANEL GUIA | AGI185 | 185X191X19,20 |
| 288 | ANEL GUIA | AGE195 | 189X195X19,20 |
| 289 | ANEL GUIA | AGI190 | 190X196X19,20 |
| 290 | ANEL GUIA | AGE200 | 194X200X19,20 |
| 291 | ANEL GUIA | AGI195 | 195X201X19,20 |
| 292 | ANEL GUIA | AGE205 | 199X205X19,20 |
| 293 | ANEL GUIA | AGI200 | 200X206X19,20 |
| 294 | ANEL GUIA | AGE210 | 204X210X19,20 |
| 295 | ANEL GUIA | AGI205 | 205X211X19,20 |
| 296 | ANEL GUIA | AGE215 | 209X215X19,20 |
| 297 | ANEL GUIA | AGI210 | 210X216X19,20 |
| 298 | ANEL GUIA | AGE220 | 214X220X19,20 |
| 299 | ANEL GUIA | AGI215 | 215X221X19,20 |
| 300 | ANEL GUIA | AGE225 | 219X225X19,20 |
| 301 | ANEL GUIA | AGI220 | 220X226X19,20 |
| 302 | ANEL GUIA | AGE230 | 224X230X19,20 |
| 303 | ANEL GUIA | AGI225 | 225X231X19,20 |
| 304 | ANEL GUIA | AGE235 | 229X235X19,20 |
| 305 | ANEL GUIA | AGI230 | 230X236X19,20 |
| 306 | ANEL GUIA | AGE240 | 234X240X19,20 |
| 307 | ANEL GUIA | AGI235 | 235X241X19,20 |
| 308 | ANEL GUIA | AGE245 | 239X245X19,20 |
| 309 | ANEL GUIA | AGI240 | 240X246X19,20 |
| 310 | ANEL GUIA | AGE250 | 244X250X19,20 |
| 311 | ANEL GUIA | AGI245 | 245X251X19,20 |
| 312 | ANEL GUIA | AGE255 | 249X255X19,20 |
| 313 | ANEL GUIA | AG2500I | 250,00X255,00X15 |
| 314 | ANEL GUIA | AGI250 | 250X256X19,20 |
| 315 | ANEL GUIA | AGE260 | 254X260X19,20 |
| 316 | ANEL GUIA | AGI255 | 255X261X19,20 |
| 317 | ANEL GUIA | AGE265 | 259X265X19,20 |
| 318 | ANEL GUIA | AGI260 | 260X266X19,20 |
| 319 | ANEL GUIA | AGE270 | 264X270X19,20 |
| 320 | ANEL GUIA | AGI265 | 265X271X19,20 |
| 321 | ANEL GUIA | AGE275 | 269X275X19,20 |
| 322 | ANEL GUIA | AGI270 | 270X276X19,20 |
| 323 | ANEL GUIA | AGE280 | 274X280X19,20 |
| 324 | ANEL GUIA | AGI275 | 275X281X19,20 |



| POS. | DESIGNAÇÃO | REFERÊNCIA | MEDIDA |
|------|------------|---------------|----------------------|
| 325 | ANEL GUIA | AGE285 | 279X285X19,20 |
| 326 | ANEL GUIA | AGI280 | 280X286X19,20 |
| 327 | ANEL GUIA | AGE290 | 284X290X19,20 |
| 328 | ANEL GUIA | AGI285 | 285X291X19,20 |
| 329 | ANEL GUIA | AGE295 | 289X295X19,20 |
| 330 | ANEL GUIA | AGI290 | 290X296X19,20 |
| 331 | ANEL GUIA | AGE300 | 295X300X19,20 |
| 332 | ANEL GUIA | AGI295 | 295X301X19,20 |
| 333 | ANEL GUIA | AGI300 | 300X306X19,20 |

